


Oldindan yuklangan IOL in'ektsiya tizimi NP-1 / NP-1C



- Silliqlik in'ektsiya
- Oddiy ikki bosqichli jarayon
- Past diopriyalik IOL'lar ham mavjud
- Ajoyib intrakapsulyar turg'unlik

Qanday ishlaydi



Dual silicone ring

Ikki silikon halqa — injektor ichida IOL'ni barqaror ushlab turadi va sillikli in'ektsiyani ta'minlaydi.

Texnik xususiyatlari

Mahsulot nomi	NP-1: NexLoad NP · NP-1C: NexLoad NP Clear
Yuklangan linza	NP-1: Nex-Acri AA 1P (Aktis SP) · NP-1C: Nex-Acri 1P (Aktis SP)
Linza modeli	NP-1: NS-60YG · NP-1C: NS-60G
Umumiy uzunlik	13.0 mm
Optik qism diametri	6.0 mm
Optik qism materiali	NP-1: sariq rangli gidrofob yumshoq akril · NP-1C: gidrofob yumshoq akril
Gaptik materiali	NP-1: sariq rangli gidrofob yumshoq akril · NP-1C: gidrofob yumshoq akril
Gaptik burchagi	0°
A-konstanta (ma'lumot uchun)	119.1
Kutilayotgan old kamera chuqurligi (ma'lumot uchun)	5.7 mm
Dioptriya diapazoni	1.0 dan 30.0 D gacha
Dioptriya qadami	0.5 D qadam: 5.0 dan 27.0 D gacha; 1.0 D qadam: 1.0 dan 5.0 D gacha va 27.0 dan 30.0 D gacha

To'liq katalog va narx so'rash: medkatalog.vercel.app